





ES980 Flexible Edge Seal

This product must be installed to allow the proper opening and closing of the door assembly with a minimal amount of force. The door assembly should be checked periodically to insure proper operation.

Tools required

- Tape measure
- Knife or scissors



Installation instructions

This product has been designed to provide an effective fire seal in the gap around a fire-rated door and/or at the meeting stile between a pair of fire-rated doors.

ES980 is to be installed as illustrated above, around the perimeter of the door assembly.

Care should be taken to install this product without stretching or damaging it in any way. The temperature of the frame should be above 40° F. The frame should be thoroughly cleaned removing dust, oil, grease or dirt. Certain paint products may make adhesion difficult. If necessary, lightly sand the painted surface and then thoroughly clean. Secure adhesion is crucial to the proper performance of this product!

1. Measure the frame at the top and both sides.
2. Cut the product to fit using a knife or scissors
3. Remove both pieces of protective backing one foot at a time.
4. Adhere seal to the exact location on frame where section is to be installed. Do not remove & relocate.
5. Inspect seal to assure proper location
6. Do not install this product to impede the opening and closing of the door assembly.
The door assembly must operate effectively.

ES980 Intumescent Fire Seal has been approved for installation with Listed Wood Core Fire Doors with Listed Wood or Steel Fire Door Frames rated 20 minutes (with hose stream), as a category G edge seal. ES980 has been approved for installation with Listed Mineral Core Fire Doors with Listed Steel Fire Door Frames rated 45 and 60 minutes as a category G edge seal when used with Lorient BW300/BW310 smoke seals. ES980 has been tested to the requirements of UL 10C (1998), ASTM E152-81a, NFPA 252 (1995). Consult Lorient or the test labs to verify the specifics of these approvals.



73NN